

**AU-BD02**

**Light-weight in-mold quality bicycle helmet -- only 7.5 USD**



**CE**

**HOT**

Size:S/M;M/L;L/XL  
Weight:220g

**ULTRA LIGHT**



<http://www.aurorasport.com/>

A horizontal sequence of 20 empty square boxes arranged in a single row.

- ဗိုလ်ချုပ်အမြတ်ဆင့်လျှပ်စီးပွဲ
  - ဗိုလ်ချုပ်အမြတ်ဆင့်လျှပ်စီးပွဲ
  - ဗိုလ်ချုပ် အမြတ်ဆင့်လျှပ်စီးပွဲ
  - ဗိုလ်ချုပ်အမြတ်ဆင့်လျှပ်စီးပွဲ
  - ဗိုလ်ချုပ်PCအမြတ်ဆင့်လျှပ်စီးပွဲ
  - ဗိုလ်ချုပ်EPSအမြတ်ဆင့်လျှပ်စီးပွဲ
  - ဗိုလ်ချုပ်အမြတ်ဆင့်လျှပ်စီးပွဲ
  - ဗိုလ်ချုပ်CE-EN1078အမြတ်ဆင့်လျှပ်စီးပွဲ

A horizontal row of 20 empty rectangular boxes, likely used for a table header or a visual representation of data.

产品名称	AU-BD02
材料	EPS&PC
认证	CE EN1078
尺寸	19mm
颜色	白色
尺寸/重量	S / M 54-58CM / M / L 58-62CM 230g
包装方式	70
MOQ	300PCS
包装结构	PP+PE+Mastercarton

A horizontal row of 20 small, identical rectangular blocks, likely representing a sequence of data or a set of items.

# Display From Different Perspectives















A horizontal row of 20 empty rectangular boxes, intended for children to write their names in, similar to a name tracing activity.

□□□□□□□□□□

A decorative horizontal bar consisting of a series of small, evenly spaced rectangular blocks.

A horizontal row of ten empty rectangular boxes, intended for handwritten responses or marks.

condierably

# Helmet Shape 101



**European Headform**

An Oval shaped helmet is designed for a rider's head with a dimension which is considerably fit for Europeans.



**Generic headform**

A generic headform helmet is designed for a rider's head with a dimension which is slightly longer front-to-back than its side-to-side measurement.



**Asian headform**

A Round shaped helmet is designed for a rider's head with a dimension which is considerably fit for Asians.

FAQ

Q: What is the difference between European, Generic, and Asian headforms?  
A: The main difference lies in the front-to-back vs. side-to-side ratio of the head. European headforms have a narrower front-to-back ratio, while Asian headforms have a much wider front-to-back ratio. Generic headforms fall in the middle, being slightly longer front-to-back than side-to-side.

## Our In-house Testing Lab



实验室

实验室通过了ISO9001质量管理体系认证和CE欧洲安全标准认证，确保产品的高品质和安全性。


## CERTIFICATE



## CUSTOMIZE FOR BRAND



Logo style: Dome, Metal, UV-Dart sticker, Water decal..



## PRODUCTION PROCESS

客户设计 → PC设计 → PC成型 → 模具设计 → 模具设计EPS → 模具设计EPS成型 → 模具  
成型 → 模具成型 → 模具成型 → 模具成型 → 模具成型 → IQC → 检验 → 检验  
→ 检验 → 检验 → 检验 → 检验 → 检验 → 检验 → 检验 → 检验 → 检验

## Production Procedure



Silk screen



PC blister tooling



PC blister manufacture



Trimming dug hole



Eps raw material  
by different density



EPS in-mold tooling



Helmet in-mold workshop



In-mold machines



In-mold tooling



In-mold producing  
process



semi-finished In-mold  
helmet



IQC inspection



Helmet grinding



Inner padding production



Plastic injection  
workshop



Assembly line



Inside labeling



Packing



Warehouse



Installed counters

### FAQ

Q1: What is the lead time for your helmets?  
 A1: Our standard lead time is 25-30 days, but it can vary depending on the complexity of the design and the volume of production.

## SHIPPING

