

🚗 - 🚗 🚗 🚗 🚗 🚗 🚗:

| | |
|-------------|---|
| 🚗 🚗 | AU-BH12 🚗 🚗 🚗 🚗 🚗 🚗 |
| 🚗 🚗 | 🚗 🚗 EPS 🚗 (🚗 🚗 🚗 🚗) |
| 🚗 🚗 | PC (🚗 🚗 🚗 🚗) 🚗 +🚗 LED 🚗 🚗 + 🚗 🚗 🚗 |
| 🚗 🚗 | - 🚗 🚗 PC + EPS + 🚗 🚗 LED 🚗 🚗 + 🚗 |
| 🚗 🚗 | CE EN1078 |
| 🚗 🚗 | 18 🚗 🚗 |
| 🚗 🚗 | 🚗 🚗, 🚗 🚗 🚗 🚗 |
| 🚗 🚗 / 🚗 🚗 🚗 | M / L 58-62cm |
| 🚗 🚗 | 245gc |
| 🚗 🚗 🚗 🚗 | 🚗 🚗 anallergic 🚗 🚗 🚗 🚗 🚗 🚗 SAFE ADVANCED USB🚗 🚗 & A 🚗 🚗, PP 🚗 🚗 🚗 🚗 🚗 🚗 LED; 🚗 🚗 🚗 🚗, 🚗 🚗 🚗 🚗 🚗 🚗 |
| MOQ | 300PCS |
| 🚗 🚗 🚗 🚗 🚗 | PP 🚗 🚗 + 🚗 🚗 🚗 🚗 🚗 🚗 + mastercarton |

🚗 🚗 🚗 🚗 🚗 🚗 🚗 🚗:











如何 使用 头盔:

头盔, 头盔 带 & A 头盔; 头盔 24 个 头盔 头盔 头盔 头盔. 头盔 头盔 头盔 头盔 头盔 头盔 头盔 头盔 头盔 R & A 头盔

| | | | | | |
|------------------|---------|---------|---------|---------|---------|
| NYLON WEBBING | | | | | |
| | PLA2001 | PLA2135 | PLA2008 | PLA2057 | PLA2191 |
| | | | | | |
| | PLA2081 | PLA2020 | PLA2242 | PLA2179 | PLA2106 |
| | | | | | |
| PLA2051 | PLA2012 | PLA2148 | PLA2304 | PLA2204 | |
| | | | | | |
| PLA2034 | PLA2041 | PLA2273 | PLA3880 | | |

| | | | | | |
|--|--|--|--|--|-----------------|
| | | | | | LOGO STICKER |
| | | | | | |
| | | | | | |
| | | | | | |

| | | | | | | |
|--------|---------|------------|------------|------------|---------|---------|
| LINING | | | | | | |
| | PLA6000 | PLA6010-10 | PLA6211-02 | PLA6325-08 | PLA6317 | PLA6520 |


| | | | | | | |
|----------------|------|------|------|------|------|------|
| DIVIDER (1) | | | | | | |
| | -111 | -36 | -116 | -119 | -00 | -120 |
| DIVIDER (2) | | | | | | |
| | -01 | -07 | -107 | -114 | -36 | -111 |
| | | | | | | |
| | -116 | -106 | -117 | -113 | -105 | -110 |
| | | | | | | |
| -00 | -115 | -109 | -112 | -104 | | |

| | | | | | | |
|------|------|------|------|------|-----|-----------------|
| | | | | | | STRAP BUCKLE |
| -114 | -36 | -107 | -07 | -106 | -01 | |
| | | | | | | |
| -113 | -104 | -117 | -115 | -116 | -00 | |
| | | | | | | |
| -112 | -111 | -109 | | | | |

| | | | | | | |
|--------|------|------|------|------|--------|------|
| BUCKLE | | | | | | |
| | -105 | -106 | -01 | -107 | -07 | -114 |
| | | | | | | |
| -110 | -104 | -116 | -117 | -106 | -112 | |
| | | | | | | |
| -115 | -111 | -00 | -109 | ITW | MAGNET | |

| | | | | | |
|--------------------|------------|---------|------------|------------|---------|
| SIZE ADJUSTMENT | | | | | |
| | PLA5022 | PLA5073 | PLA5285 | PLA5406 | PLA5663 |
| | | | | | |
| PLA5058 | PLA5127-00 | PLA5127 | PLA5388-13 | PLA5388-01 | |

| | | | | | |
|------------|------------|------------|-------------|------------|-------|
| | | | | | VISOR |
| PLA1213-00 | PLA1213 | PLA0481-18 | PLA0481 | PLA0083-09 | |
| | | | | | |
| PLA0267 | PLA0267-07 | PLA0872A | PLA0872-113 | PLA0083 | |



The Dial of Adjustment can be interchangeable with LED light

Headform and Headform : Headform :

Headform :

Headform is a model of a human head used for testing and fitting helmets.

headform :

headform is a model of a human head used for testing and fitting helmets.

headform :

Headform is a model of a human head used for testing and fitting helmets.

Helmet Shape 101



European Headform

An Oval shaped helmet is designed for a rider's head with a dimension which is considerably fit for Europeans.

Generic headform

A generic headform helmet is designed for a rider's head with a dimension which is slightly longer front-to-back than its side-to-side measurement.

Asian headform

A Round shaped helmet is designed for a rider's head with a dimension which is considerably fit for Asians.

Headform and Headform :

Headform is a model of a human head used for testing and fitting helmets.

& A 00000; 00 0 00! 000 00 0000 0000 0000 0000 00 00 0000 00 0 0 00000 00000 0000 00 0 0 00000 0 0000, 00 0000 00 0 0000 0 00000!

Our In-house Testing Lab



00:

0000 0000000 : 0000 ISO9001, 00 00, CE 0000 0000, 0000 0000 00 0000 00 0 0 0000 00 0000 00 0000 0000

CERTIFICATE



15

15 R & A, D, 15

CUSTOMIZE FOR BRAND



Logo style: Dome, Metal, UV-Dart sticker, Water decal.



PC 3D 3D 3D :

PC 3D → PC 3D → PC 3D → 3D 3D 3D → 3D 3D 3D EPS 3D → EPS - 3D 3D → 3D 3D 3D → 3D 3D → - 3D 3D → 3D 3D 3D → 3D 3D → IQC 3D → 3D 3D → 3D 3D 3D → 3D 3D 3D → 3D 3D → 3D 3D → 3D → 3D → 3D 3D.

Production Procedure



Silk screen



PC blister tooling



PC blister manufacture



Trimming dug hole



Eps raw material by different density



EPS in-mold tooling



Helmet in-mold workshop



In-mold machines



In-mold tooling



In-mold producing process



semi-finished In-mold helmet



IQC inspection



Helmet grinding



Inner padding production



Plastic injection workshop



Assembly line



Inside labeling



Packing



Warehouse



Installed counters

□□ □□ :

□□ □□, □□□□ & A; □□ □□□ □ □□□ □□ □ □□□! □□□□ □□□□ □□□ □□ □□□□; □□□□ □□□□ □□ □□□□ □□ □□□□! □□□□ □□ □□ □□ □□ & A □□□□ □□□□ □□; □□ □□□□, □□□□ □□ □□□□ □□□□ □□ □□□□ □□□□! □□□□ □□, □□ □□ □□□□ □□ □□ □□□□!

SHIPPING

