

PC 1000

- 顏色 選擇: 1 種, 2 種 (選擇)
- 顏色 選擇: 選擇
- 顏色 選擇: AU-M01
- 顏色: PC + EPS
- 顏色: 顏色 顏色 顏色
- 顏色: PC + EPS
- 顏色: 顏色 顏色 顏色
- 顏色: 57-61 cm
- 顏色: 275 g
- 顏色: 1 種 顏色
- 顏色: 14
- 顏色: 顏色 顏色 顏色 顏色 顏色 顏色 顏色 顏色 顏色 顏色
- 顏色: 顏色 顏色 顏色 顏色 顏色
- 顏色: 顏色, 顏色, 顏色, 顏色
- 顏色: 顏色-顏色 顏色 顏色 顏色 & 顏色

PC 1000

顏色 顏色 顏色: PP 顏色, 顏色 顏色, 顏色

PC 1000, 顏色 顏色 顏色 顏色

顏色 顏色

顏色	顏色	(顏色 顏色)
顏色 顏色	顏色 顏色 顏色	
顏色	EPS 顏色 + PC 顏色	EPS 顏色, EPS + PC inmould 顏色 顏色 顏色 顏色 顏色 顏色 顏色 顏色; 顏色 顏色 顏色; 顏色 顏色 顏色 顏色
顏色	57-61 cm	顏色 顏色 顏色 顏色 顏色 顏色
顏色	顏色	UV DRT, 顏色 顏色
MOQ	2000 pc	
顏色 顏色	65 cm * 57 cm * 46 c m	72 cm * 57 c * 59 cm
顏色 顏色	1 顏色	顏色 顏色 顏色
顏色 顏色 顏色	顏色 45 顏色	顏色 顏色 顏色 顏色 顏色 顏色 顏色 顏色 顏色 顏色

0000.0000

0000 00 OEM 0000 000000 0000 00 00000 00 00 00 0000 0 0 00, 0000 0000 0000 0 00000. 0000 0000 00 0 00 0000 0000 00 0 00 0 00 00 00 00:

1, 0000 00 00000000.

2, 0000 00 00 0 00 0 00000000.

3, 0000 00 00000000.

0000 00 4 00 00 00000000.

5, 0000 00 00000000.


6, 00 0 0000, 0000, PE 0 0, 000000 0000 0000 0000 00.

00:









headform:

A considerably different shape than the European headform.

Helmet Shape 101



European Headform

An Oval shaped helmet is designed for a rider's head with a dimension which is considerably fit for Europeans.

Generic headform

A generic headform helmet is designed for a rider's head with a dimension which is slightly longer front-to-back than its side-to-side measurement.

Asian headform

A Round shaped helmet is designed for a rider's head with a dimension which is considerably fit for Asians.

:


adjust the helmet:

1: Make sure the helmet is on your head, and the chin strap is properly adjusted.

2. Use the dial indicator to adjust the helmet.

3. Use the dial indicator to adjust the helmet.

4. Use the dial indicator to adjust the helmet.



如何正确佩戴头盔：

佩戴头盔 → PC 头盔 → PC 头盔 → 头盔 头盔 头盔 → 头盔 头盔 EPS 头盔 → EPS 头盔 头盔 → 头盔 头盔 头盔 → 头盔 头盔 → 头盔 头盔 → 头盔 头盔 → IQC 头盔 → 头盔 头盔 → 头盔 头盔 → 头盔 头盔 头盔 → 头盔 头盔 → 头盔 头盔 → 头盔 头盔 → 头盔 头盔。



Eps raw material
by different density



In-mold producing process



Plastic injection workshop



Installed counters

Our In-house Testing Lab



Our in-house testing lab is equipped with state-of-the-art equipment to ensure the highest quality and safety standards for our products. We conduct rigorous testing on all components, from individual parts to complete assemblies, to identify potential weaknesses and improve our designs. This comprehensive testing process allows us to deliver reliable and durable products to our customers.

**WESTERN
UNION**



በጥቅም ላይ የዋለው የጥናት ሪፖርት 15 ምሳሌዎችን ያሳያል፡፡ ለ R & D ምሳሌዎች፣ የጥናት ሪፖርት ምሳሌዎችን ያሳያል፡፡

በግልጽ በሚታወቅ ሁኔታ ላይ ስለሚገኝ ማረጋገጥ ይቻላል፡፡