

## □□□□ □□ □□□□ □□□□ □□□□ □□□□



### □□ □ □ □□ □□□ □□:

- □□□ □, □□ □□ □□ □□□□ □□ □□ □□□.
- □□ □□:□ □□□□ □□ □□ □□□ □□□ □□, □□ □□□□, □□□□ □ □□ □□.
- □□, □ □□ □□, □□ □□ □□ □.
- eco □□ □ □ □ □□ □□ pc □□.
- eps □□□ □□□□ □□ □□,

-**0000**: 00 00 0000 00 00 0000 0 00; 0000 0000 00; 0000 0000 00 00 00 0000 0000 0000;

-**0000**: 00 00 0000 00 00 0 0 0 **EN1078**.

**00 000000 00:**

00 00	au-bm17 0000 00
00	eps 0 0 pc 00 00
00	ce en1078
00 00	21 00 0000
0 0	0 0, 0000 00
0000/00 00	m/l (58-62 c m)
0 000	250 g
00 0 00	0 0000, 0000 00 00 00 00 00, 000000 0000 0 00 00, 0000 00 0 usb led 0, <a href="#">0000-0-00-00</a>
moq	300pcs
0000 00 00	pp 0 0 + 000000 00 00 00 + 0000 0 0

**00 00 000000 00:**







## 000 00 0000:

0000 000 24 0 00 000 00 0 000 00 0 0 00 00000. 000 0 0000 00 000-00 00 00 00 000 000 0000 000 00, 000 00 0 000 0 0 000 000 000 0 00 000. 000 00 00000 00 00 00000 00 00, 000 00 00, 00 00 00 00, 00, 00 0000, 00, 0 000, 00, 00 00 00 0000 000 0 00, 000 00 00 0 0 00 00 00 0 0 00 0000 00 00 0000 0 0 0000.

NYLON WEBBING					
	PLA2001	PLA2135	PLA2008	PLA2057	PLA2191
	PLA2081	PLA2020	PLA2242	PLA2179	PLA2106
PLA2051	PLA2012	PLA2148	PLA2304	PLA2204	
PLA2034	PLA2041	PLA2273	PLA3880		

					LOGO STICKER

LINING						
	PLA6000	PLA6010-10	PLA6211-02	PLA6325-08	PLA6317	PLA6520


DIVIDER (1)						
	-111	-36	-116	-119	-00	-120
DIVIDER (2)						
	-01	-07	-107	-114	-36	-111
	-116	-106	-117	-113	-105	-110
-00	-115	-109	-112	-104		

						STRAP BUCKLE
-114	-36	-107	-07	-106	-01	
-113	-104	-117	-115	-116	-00	
-112	-111	-109				

BUCKLE						
	-105	-106	-01	-107	-07	-114
-110	-104	-116	-117	-106	-112	
-115	-111	-00	-109	ITW	MAGNET	

SIZE ADJUSTMENT					
	PLA5022	PLA5073	PLA5285	PLA5406	PLA5663
PLA5058	PLA5127-00	PLA5127	PLA5388-13	PLA5388-01	

					VISOR
PLA1213-00	PLA1213	PLA0481-18	PLA0481	PLA0083-09	
PLA0267	PLA0267-07	PLA0872A	PLA0872-113	PLA0083	



The Dial of Adjustment can be interchangeable with LED light

**How to adjust your helmet:**

Step 1:

Adjust the dial to fit your head. The dial should be centered on your forehead.

Step 2:

Adjust the chin strap. The strap should be snug against your chin.

Step 3:

Check the fit. The helmet should sit level on your head and not rock forward or backward.

# Helmet Shape 101



**European Headform**

An Oval shaped helmet is designed for a rider's head with a dimension which is considerably fit for Europeans.

**Generic headform**

A generic headform helmet is designed for a rider's head with a dimension which is slightly longer front-to-back than its side-to-side measurement.

**Asian headform**

A Round shaped helmet is designed for a rider's head with a dimension which is considerably fit for Asians.

**How to choose a helmet:**

When choosing a helmet, consider your head shape, the helmet's safety features, and the fit. A helmet should fit snugly and comfortably. Always use proper adjustment techniques.

我們提供全面的測試服務! 我們提供全面的測試服務, 包括: 碰撞測試, 耐久測試, 靜態測試, 動態測試, 環境測試, 材料測試, 組裝測試, 性能測試, 安全測試, 等等。我們擁有先進的測試設備和專業技術, 為您提供最優質的測試服務。

## Our In-house Testing Lab



☐☐:

我們提供全面的測試服務: iso9001, 碰撞測試, 耐久測試, 靜態測試, 動態測試, 環境測試, 材料測試, 組裝測試, 性能測試, 安全測試, 等等。我們擁有先進的測試設備和專業技術, 為您提供最優質的測試服務。



# CERTIFICATE



## 公司优势:

公司拥有 15 年研发经验，拥有 r&d 团队，为客户提供专业的技术支持和解决方案。



# Production Procedure



Silk screen



PC blister tooling



PC blister manufacture



Trimming dug hole



Eps raw material by different density



EPS in-mold tooling



Helmet in-mold workshop



In-mold machines



In-mold tooling



In-mold producing process



semi-finished In-mold helmet



IQC inspection



Helmet grinding



Inner padding production



Plastic injection workshop



Assembly line



Inside labeling



Packing



Warehouse



Installed counters

□ □□:

□ □□ □□□ □□□□:

-□□: □□□ □□ □□ □ □□□ □□□ □□

-oem □ odm: □□□ □□□ □□ □□□ □□□ □□□ □ □□□□

-□□ □ □□ □: □□□ □ □□□□ □□ □□□ □

-□□: □□□ □□□ □□□ □□ □□□, □□□□□ □□□ □□ □□

-□□: □□□ □□ □□□ □□□ □□□□□ □□ □ □□□□.

-□□□: □□ □ □□ □ □□□, □□□ □□



QUALITY

With strict quality management system and first-class products



OEM&ODM

We can provide OEM and ODM service for customers



R&D TEAM

With professional and strong technical development team



PRICE

We have our own production line, to reduce the price to a minimum



PATENT

We constantly introduce patented technology products



SERVICE

Perfect after-sales service, so customer satisfaction

公司优势:

我们拥有专业的研发团队 & 严格的质量管理体系! 我们拥有自己的生产线, 可以降低价格到最低! 我们拥有专业的售后服务团队, 所以客户满意度! 我们拥有专业的研发团队, 所以客户满意度!

### PAYMENT

- We accept T/T ,Western Union or Paypal before production
- If buyers have any problems about payment , please contact us ASAP



### SHIPPING

- 3-15 working days since payment receipt (based on actual quantity)
- Tracking No. will be sent to you after delivery . And you will get every important shipping status by email.

