

beanie~ 5.0. enjoying hand-free Hi-Fi



品名	Warm beanie hat with Bluetooth 5.0
Textile material	60% Acrylicand 40% Polyester
Bluetooth version	5.0.
传输距离	Up to 10m
Talk time	Up to 10h
待机时间	Up to 60h
Charge time	2h
厚度	06mm
S/N	>95db@32ohm/5mW
Frequency response	180- 20 kHz
电池	Li-ion 3.7 VI 150 mAh
配件	Music hat and Micro USB cable

beanie~ 5.0.



☐☐:

Wireless bluetooth beanie keeps your head very warm and you are able to listen to your favorite songs without disrupting anyone else. The sound quality is great, and the speaker is removable for washing beanie.



## PREMIUM AUDIO QUALITY

Premium Audio Quality – Built with 12.5mm stereo speaker magnets and microphone that deliver clear and high quality digital sound. Universal Bluetooth technology with forward/backward compatibility to connect to all Bluetooth enabled media player devices and automatically connect to your last paired device.



## 产品功能

The simple panel display on the ear of the Bluetooth wireless knitted beanie has 3-prompt buttons and an LED indicator light. Go pass the basic controls of pausing/playing music and be able to answer calls, skip songs, and control the volume.





☐☐ looking.

☐☐☐☐☐☐☐☐.



## RECHARGABLE AND REMOVABLE

The Bluetooth beanie features headphone slits that make the headphones easy-to-remove and reinstall.



[customization](#)

oem.~ customization needed.

# Superior Features

---



Up to **104db** HD  
Stereo Sound



Rechargeable  
Battery



Washable Material



Hands Free Calling




**8** Hours Talking  
Playing Time



□□□□□□

It can be used for Hiking, camping, fishing, jogging. [A special gift for your loved one.](#)





## Our test lab:

For the production of high-quality helmets, to learn not only from the theory of design, but also to make progress from the result of testing! Therefore our factory equipped with a professional testing laboratory, that each design is a practical and accessible! Our test standard is more stringent than the requirements of the relevant certificate, therefore we can promise a model that we can certainly test the corresponding third party!

## Our In-house Testing Lab



## Factory photos:

Production procedure of the helmet is as below:

PC 100 → PC blister tooling → PC 1000 100 → Crop dug a hole → EPS raw material under different density → EPS-mold machining → the helmet in the mold workshop → in the moulding machines → Mold Machining → mold produce process → semi-finished product in the mold helmet → IQC 100 → 100, 10000 → 1000 100 100 → 10000 100 100 → 100 100 →in describing →