

## 物料清單

- 物料: 鋼, 鋼 (鋼)
- 物料: HaoJiGuang
- 物料: AU-S02
- 物料: EPS + PC
- 物料: 鋼 鋼
- 物料 : 鋼
- 物料: CE, EN, CPSC
- 物料: 鋼 鋼
- 物料: EPS + PC 鋼 鋼
- 鋼: 鋼
- 物料: M : 56-58CM, L (58-62 CM)
- 物料: 鋼 鋼 鋼 鋼 鋼 鋼
- OEM 鋼 REQ 鋼 MOQ : 1000 鋼
- 鋼 鋼 : 鋼, 鋼 鋼 鋼 鋼
- accessoris : 鋼 鋼, 鋼 鋼 鋼, PA 鋼

## 鋼 & A; 鋼

鋼 鋼 鋼 : 1. PP 鋼, PVC 鋼, 鋼 UVEX 鋼 鋼 鋼, 鋼 鋼 鋼 鋼 鋼 鋼 鋼 鋼;  
2. 鋼 鋼 鋼

鋼 鋼 鋼 : 鋼 鋼 15 鋼 鋼

### - 鋼 鋼 鋼 鋼 :

1. 鋼 鋼 鋼 鋼 鋼 鋼 鋼 鋼 鋼 鋼 鋼 鋼, 鋼 鋼 鋼 鋼

2. - 鋼 鋼 : 鋼 鋼 鋼 鋼, 鋼 鋼 鋼 鋼 鋼 鋼 鋼 鋼,

3. Thicken PC 鋼, 鋼 鋼 鋼 鋼 鋼.

4. 鋼 鋼 鋼 EPS 鋼, 鋼, 鋼, 鋼 鋼 鋼 鋼.

5. with 鋼 鋼 鋼 鋼, PA 鋼, 鋼 鋼

鋼 鋼 鋼 6. Lining 鋼 鋼 鋼 鋼 鋼 鋼.

- 00 00 000 00.

0	000	00 00
1. 00 00	00 00, 0 00, 000 00 00	Casnd 00, 000 00, 00 000 00, 00 000 00
2. Model 0	AU-S03	
3. Material	00 000 EPS 000 + PC 0	EPS 00 00, EPS 0 + ABS 00, 00 000 00 0
4. 00		00 pantone 00
5. Head 00	M : 56-58CM, L (58-62 CM)	00 00 00 0 000 00
7. Logo	00	00 00 00 000 0
8. MOQ	1000PCS	
9. Carton 00	65cm * 57cm 0 * 0 46cm	72cm * 57C 0 * 0 59cm
10. Packing	1PCS / PPB / 00 00	10PCS 000 CTN
11. Price 00	00 00	
12. Shipping 00	00 00 000 00	000
13. Payment 00	000	T / T, 000 000, L / C
14. Sample 00	4~70	000 00 00 00000 0
15. Production 00 00	20~300 0	00 00 000 00 0, 00 00 000 00.
16. Gender	00 00	
17. Main 00	00, 00, 000. ASTM 0 F1447-06 ASTM 0 F1952-09 ASTM 0 F1492-08 ASTM 0 F1898-08 ASTM F1163-04a ASTM 0 F2040-11 ASTMF1045-2007	
18. Our 00 00 00	CPSC 1203 BS EN1078 : 2012 BS EN1080 : 2002 + A2 : 2005 + A1 1997 BS EN1384 : 2002 + A1 1997 BS EN1077 : 2007 BS EN1385-1998 + A1 : 2005 EN ISO10256 : 2003 AS / NZS2063-2008 + A1 : 2009 2006 : NZS3838 / AS	
19. Our 00	000 000 1. 00 00 2. 00 000 0 00 000 00 3. 00 00 4. 0000 0 00 00 00 5. 00 00 00 6. 00	

00:







0000, 0000 00 & A 000; 0 00 24 0 00 000 00 000 00. 000 000 R & A0 00 0 0 00 0000 00 000 00 00 0000 00  
0 00 0000 0000 000 0 0000; D support.We 0000 00 00 0000 0000 0000 0000 00 00 00 0000 00, 00 0000 00  
00000 00, 00 00 0000, 0000 00, 00 0000 00 00, 0000 00000 00 00 00 00000 00 00 00 0 0 00000.



NYLON WEBBING					
	PLA2001	PLA2135	PLA2008	PLA2057	PLA2191
	PLA2081	PLA2020	PLA2242	PLA2179	PLA2106
PLA2051	PLA2012	PLA2148	PLA2304	PLA2204	
PLA2034	PLA2041	PLA2273	PLA3880		

					LOGO STICKER

LINING						
	PLA6000	PLA6010-10	PLA6211-02	PLA6325-08	PLA6317	PLA6520

DIVIDER (1)						
	-111	-36	-116	-119	-00	-120
DIVIDER (2)						
	-01	-07	-107	-114	-36	-111
	-116	-106	-117	-113	-105	-110
-00	-115	-109	-112	-104		

						STRAP BUCKLE
-114	-36	-107	-07	-106	-01	
-113	-104	-117	-115	-116	-00	
-112	-111	-109				

BUCKLE						
	-105	-106	-01	-107	-07	-114
-110	-104	-116	-117	-106	-112	
-115	-111	-00	-109	ITW	MAGNET	

SIZE ADJUSTMENT					
	PLA5022	PLA5073	PLA5285	PLA5406	PLA5663
PLA5058	PLA5127-00	PLA5127	PLA5388-13	PLA5388-01	

					VISOR
PLA1213-00	PLA1213	PLA0481-18	PLA0481	PLA0083-09	
PLA0267	PLA0267-07	PLA0872A	PLA0872-113	PLA0083	

## Headform

Headform :

Headform is a model of a human head used for testing and fitting helmets.

headform :

Headform is a model of a human head used for testing and fitting helmets.

headform :

Headform is a model of a human head used for testing and fitting helmets.

# Helmet Shape 101



### European Headform

An Oval shaped helmet is designed for a rider's head with a dimension which is considerably fit for Europeans.

### Generic headform

A generic headform helmet is designed for a rider's head with a dimension which is slightly longer front-to-back than its side-to-side measurement.

### Asian headform

A Round shaped helmet is designed for a rider's head with a dimension which is considerably fit for Asians.

:

Headform is a model of a human head used for testing and fitting helmets.

1. Headform is a model of a human head used for testing and fitting helmets.

2. Adjust the headform to fit the helmet.

3. Adjusting the headform to fit the helmet.





# Our In-house Testing Lab



Our in-house testing lab is equipped with advanced equipment for comprehensive product testing. We offer a wide range of services, including impact testing, vibration testing, and environmental testing. Our experienced technicians provide expert assistance throughout the testing process. Make your product testing more efficient and reliable with our state-of-the-art facilities.





# FOCUS ON THE USER EXPERIENCE

☐ 如何 如何?

---- 如何 如何 如何 如何 如何

如何 : 如何 如何 如何 如何 如何

OEM & A, ODM : 如何 如何 OEM 如何 ODM 如何 如何 如何

R & A, D 如何 : 如何 如何 如何 如何 如何

如何 : 如何 如何 如何 如何 如何, 如何 如何 如何 如何

如何 : 如何 如何 如何 如何 如何

如何 : 如何 如何 如何, 如何 如何

如何 如何 如何 如何 如何 15 如何 如何 如何 如何 如何. 如何 如何 R & A, 如何 如何 D 如何, 如何 如何 如何 如何 如何 如何 如何 如何 如何 如何 如何 如何 如何 如何 如何.